# EKASTU | Safety WIR PRODUZIEREN SICHERHEIT!

**Technical Data Sheet** 

Polimask ALFA



Order no.: 466 620

### **Product designation:**

# Half Mask Polimask ALFA

In connection with respiratory filter (standard thread DIN EN 148-1 and weight of filter <300 g) as filtering device, in connection with powered filtering device as filtering device, in connection with compressed air line device as breathing apparatus. Use filter >300g only in connection with Filter carrying device S/03016. The scope of protection is determines by the product information, technical standards and valid application rules.



# **DESCRIPTION**

- · Adaptability to any kind of face with a good sealing ability
- Anatomically shaped mask body made of non-irritating, soft EPDM
- · Low breathing resistance
- Compatible with the use of glasses and goggles
- Easy donning and doffing
- Easy maintenance, washing and disinfection

# **I MAIN FEATURES**

Faceblank made of soft EPDM

Large internal sealing flap that allows a perfect adaptability to the face and an excellent seal



Comfortable innovative 4-point harness ensures optimal weight distribution and quick donning of the half mask

Threaded connector conforming with European EN 148/1 standard. For use with one filter series DIRIN 230

# **I PERFORMANCES**



Comfort



Ergonomics



Sturdiness



Easy maintenance

# I APPLICATION FIELDS



Industry



Hospital





### **MATERIALS**

· Faceblank: Ethylene-Propylene-Diene-Mixture (EPDM)

· Fastener for head harness: Plastc (ABS)

• Harness: Textile elastic band / Polypropylene (PP)

Inhalation valve: RubberExhalation valve: Rubber

• Exhalation valve fit: Plastic (ABS)

• Connector: Polypropylene (PP)

### WEIGHT

• approx.: 160 g

# **MARKING**

- Trade mark of manufacturer (LOGO)
- · Product designation
- · Applied standard
- · Manufacture year and -month
- CE-Identification
- · Notified body
- · Type identifying marking

### **DONNING AND USING**

- · Take the Half mask from the Packing and/or Storage container directly before use
- · Use the Half mask in accordance with the information brochure

### **STORAGE**

- · Ambient temperature. Protect against cold, heat and humidity
- · Consider conditions noted on the packaging

### **CERTIFICATIONS**

- · The mask is certified according to EN 140
- · For use with particle, gas and combined filter of the series DIRIN 230
- · Certified according to European Regulation (EU) 2016/425

## **USER REFERENCES**

EKASTU Safety GmbH guarantees the indicated achievement according to class and type. It is to be noted that the laboratory test values can considerably deviate from those, which are reached in practice. The user must read and understand all functional information. Use the Respiratory protective devices with this information brochure, the relevant valid statutory regulations and the safety requirements of the profession associations, particularly the regulations for use in accordance with DGUV Rule 112-190 resp. DIN EN 529 "Respiratory protective devices – recommendation for selection, use, care and maintenance – guidelines".

TD 466620 English\_06-04.24

Internet: www.ekastu.de

eMail: info@ekastu.de

EKASTU Safety GmbH Schänzle 8 • D-71332 Waiblingen Germany Tel.: +49(0)7151 975099-0 Fax: +49(0)7151 975099-30